

piSAVE® sense Multiple port fitting 05/60 (red), 01.28.733




- Vacuum check valves which allows a few suction cups to miss the object(s) and still maintain enough vacuum level in the system with quick response and release times.
- The vacuum check valves shall be used in a centralized vacuum system, one for each suction cup.
- Designing with vacuum check valves will require a smaller vacuum pump and save energy.
- Also suitable for objects with surface leakage around the lip of the suction cup.
- Available in four sizes with different flow performance/characteristics to suit different degree of leakage on handled material and different size of cups.
- The valves are supplied separately for integration or mounted in an Al-fitting with female and male threaded connections to facilitate installation.

General

| | |
|------------------------------|---|
| Material | Al, HNBR, Nitrile (NBR), Thermoplastic Polyurethane (TPE-U) |
| Pump flow/cup minimum | 1.12 scfm |
| Pump flow/cup to close valve | 3.23 scfm |
| Temperature | -4 – 176 °F |
| Valve colour | Red |
| Weight | 0.73 oz |

Dimensional drawings



Accessories

| | Part no. |
|----------------------------------|-----------|
| piSAVE® sense Assembly tool 16mm | 02.02.589 |